

Correct O-ring Selection when Installing an iMeter®

In June 2011, Wayne® made a design change to the “remote inlet casting” located directly under the iMeter™ in Vista™ and Ovation® dispensers. The photos on this page illustrate the old and new type inlet castings.

Caution:

The two types of castings require different O-ring seals. The O-rings are NOT interchangeable between the old and new type inlet castings. The new type inlet casting requires O-rings which are slightly thicker than those required with the old type casting. Using the incorrect O-ring seals may result in leakage.

The PMP installation kit received in this package contains either Black and White seals or Blue and Red seals. The black or blue seals are to be used with the old type inlet casting. The red or white seals are to be used with the new inlet casting.

O-rings used here are NOT interchangeable between old and new inlet castings.



Old Remote Inlet Casting

Must use the BLACK or BLUE O-ring seals

New Remote Inlet Casting

Must use the WHITE or RED O-ring seals



iMeter shown mounted to Old Remote Inlet Casting



iMeter shown mounted to New Remote Inlet Casting

All product or company's names, trade names, trademarks, parts numbers and part descriptions may be the trademarks of their respective owners, and are used for reference or identification purposes only. PMP does not claim any right to or affiliation with such owners. The PMP product described here is manufactured or remanufactured and sold by PMP and is not the product of any other identified manufacturer.



PMP CORPORATION
P.O. Box 422 • 25 Security Drive
Avon, CT 06001

Local: 860-677-9656
Toll Free: 800-243-6628
Toll Free Fax: 888-674-0196
Web: www.pmp-corp.com
E-mail: sales@pmp-corp.com



© PMP CORP